

MATERIAL LIST

TOTAL SHEETS 2

FOR

REVISION C

TMC MODEL - GPT-40K*5

TITLE- RADIO XMTR, BASIC

USED ON MODEL -

All GPT-40K's

CONSISTS OF SUPPORTING LISTS

AM115	AX104
AM122	AX107
AP116-2	AX138-2
AP117	AX181
AP118-2	AX182
AR116	AX208
AR161	AX210
AT106	AX211
AX212	AX213
AX504	AX510
AX511	AX557-2
RFC-1B	

COMPILED	ENG. COORD
CHECKED	
ENG APPR	
FNL APPR	J. SABATINO
ISS DATE	1/20/67

MATERIAL LIST

GPT-40K*5
REV.C

PAGE 2

OF 2

PART NUMBER	DESCRIPTION	USED ON	QUANTITY	QUANTITY PER UNIT	REFERENCE SYMBOLS	SPECIAL NOTES REFER TO S 1200
AX212	CROWBAR DRAWER	GPT-40K*5	1	1*	8300	1
AX213	PS CONT PNL	GPT-40K*5	1	1*	8500	1
AX504	MAIN PWR PNL	GPT-40K*5	1	1*	1000	1
AX510	PA SECTION, 10K	GPT-40K*5	1	1*	900	1
AX511	PA SECTION, 40K	GPT-40K*5	1	1*	7300	1
AX557-2	MN FR FNL ASSY	GPT-40K*5	1	1*	1000	1
CHXXX	CHART, TUNING	GPT-40K*5	1	1*		54
CH352	CHART SYSTEM	GPT-40K*5	1	1*		
CKXXX	DIAG, WRG, AUX	GPT-40K*5	1	1*		54
CK1067	DIAG, SCHEM, 10K	GPT-40K*5	1	1*		
CK1068	DIAG, SCHEM, PA	GPT-40K*5	1	1*		
CK1069	DIAG, SCHEM, PS	GPT-40K*5	1	1*		
RFC-1B	RF AMPL	GPT-40K*5	1	1*	200	1
S540	TEST PROC	GPT-40K*5	1	1*		
4/7/66 REV A	EMN 16059			*		
7/11/66 REV B	EMN 16490			*		
12/27/66 REV C	EMN 17570			*		

MATERIAL LIST

GPT-40K*5
REV.C

PAGE 1

OF 2

PART NUMBER	DESCRIPTION	USED ON	QUANTITY	QUANTITY PER UNIT	REFERENCE SYMBOLS	SPECIAL NOTES REFER TO S 1200
AM115	PA FR MTR BOX	GPT-40K*5	1	1*	7200	1
AM122	MN FR MTR BOX	GPT-40K*5	1	1*	1000	1
APXXX	HVR, 40K	GPT-40K*5	1	1*	8400	54
AP116-2	PA FRAME ASSY	GPT-40K*5	1	1*	7100	1
AP117	BIAS SUPPLY	GPT-40K*5	1	1*	7500	1
AP118-2	PS FRAME ASSY	GPT-40K*5	1	1*	8100	1
AR116	RELAY PNL, 40K	GPT-40K*5	1	1*	7600	1
AR161	RELAY PNL, 10K	GPT-40K*5	1	1*	700	1
AT106	ANT.TUN/MTR BX	GPT-40K*5	1	1*	8200	1
AXXXX	ENCL/ACCESS.	GPT-40K*5	1		3000	54
		GPT-40K*5	1		3000	54
		GPT-40K*5	1	3*	600	54
AX104	PNL CHAS ASSY	GPT-40K*5	1	1*	2000	1
AX107	AUX MTR BOX	GPT-40K*5	1	1*	3000	1
AX138-2	MAIN PWR SUP.	GPT-40K*5	1	1*	800	1
AX181	AUX FR SUBASSY	GPT-40K*5	1	1*	3000	1
AX182	MN FR SUBASSY	GPT-40K*5	1	1*	1000	1
AX208	PA FR SUBASSY	GPT-40K*5	1	1*	7100	1
AX210	PA FR CONT PNL	GPT-40K*5	1	1*	7400	1
AX211	PS FR SUBASSY	GPT-40K*5	1	1*	8100	1